Pro**Labs**

LR-XFP-10G-NP

MSA and TAA 10GBase-LR XFP Transceiver Low Power (SMF, 1310nm, 10km, LC, DOM)

Features:

- INF-8077i Compliance
- Duplex LC Connector
- Single-mode Fiber
- Commercial Temperature 0 to 70 Celsius
- Hot Pluggable
- Metal with Lower EMI
- Excellent ESD Protection
- RoHS Compliant and Lead Free



Applications:

- 10GBase-LR Ethernet
- 8x/10x Fibre Channel
- Access, Datacenter and Enterprise
- Mobile Fronthaul CPRI/OBSAI

Product Description

This MSA Compliant XFP transceiver provides 10GBase-LR throughput up to 10km over single-mode fiber (SMF) using a wavelength of 1310nm via an LC connector. It is built to MSA standards and is uniquely serialized and data-traffic and application tested to ensure that they will integrate into your network seamlessly. Digital optical monitoring (DOM) support is also present to allow access to real-time operating parameters. This transceiver is Trade Agreements Act (TAA) compliant. We stand behind the quality of our products and proudly offer a limited lifetime warranty.

ProLabs' transceivers are RoHS compliant and lead-free.

TAA refers to the Trade Agreements Act (19 U.S.C. & 2501-2581), which is intended to foster fair and open international trade. TAA requires that the U.S. Government may acquire only "U.S. – made or designated country end products."



Rev. 080823

Absolute Maximum Ratings

Parameter	Symbol	Min.	Max.	Unit
Maximum Supply Voltage	Vcc3	-0.5	3.6	V
	Vcc5	-0.5	6	V
Storage Temperature	TS	-40	85	°C
Operating Temperature	ТО	-5	70	°C
Operating Humidity	RH	5	85	%
Receiver power	R _{MAX}		0.5	dBm
Maximum bitrate	B _{max}		11.3	Gbps

Electrical Characteristics (TOP=25°C, Vcc=3.3Volts)

Parameter	Symbol	Min.	Тур.	Max.	Unit	Notes
Power Supply Voltage	Vcc3	3.15	3.30	3.43	V	
	Vcc5	4.75	5.0	5.25	V	
Power Supply Current	lcc			455	mA	
Power Consumption	P _{DISS}			1.5	W	
Transmitter						
Differential data input swing	Vin, pp	120		850	mV	
Input differential impedance	Zin	80	100	120	Ω	
Receiver			·	·		
Differential data output swing	Vout, pp	300		850	mV	
Output differential impedance	Zin	80	100	120	Ω	

Optical Characteristics

Parameter	Symbol	Min.	Тур.	Max.	Unit	Notes
Transmitter						
Optical Power (average)	P _{AVE}	-3		0.5	dBm	1
Optical Modulation amplitude (OMA)	P _{OMA}	-5.2			dBm	2
Optical Extinction Ratio	ER	3.5			dB	
Optical Wavelength	Τλ	1260	1310	1355	nm	
Insertion loss	IL		0.6			
Receiver						
Receiver Sensitivity (average)	R _{AVE}			-14.4	dBm	3
Receiver Sensitivity (OMA)	R _{OMA}			-12.6		2
Receiver overload	P _{max}	0.5			dBm	4
Receiver wavelength	Rλ	1260		1565	nm	

Notes:

- 1. Coupled into a Single mode fibre
- 2. Per IEEE 802.3ae specification
- 3. Average power, back-to-back, @10.31Gbps, BER 1E-12, PRBS 231-1.
- 4. Exceeding the Receiver overload can physically damage the module. Please use appropriate attenuation.

Pin Descriptions

Symbol	Name/Descriptions	Ref.
GND	Module Ground	
Vee5	(not required)	
MOD_DESEL	Module De-select; When Held low allows the module to respond to 2-wire serial interface. LVTTL-I	
/INTERRUPT	Interrupt; Indicates presence of an important condition which can be read via the 2-wire serial interface. LVTTL-O	2
TX_DIS	Transmitter Disable. Logic1 indicates laser output disabled, LVTTL-I	
VCC5	+5V Power Supply (Not required)	
GND	Module Ground	1
VCC3	+3.3V Power Supply	
VCC3	+3.3V Power Supply	
SCL	2-Wire Serial Interface Clock. LVTTL-I	2
SDA	2-Wire Serial Interface Data Line. LVTTL-I/O	2
MOD_Abs	Indicates Module is not present. Grounded in the Module. LVTTL-O	2
MOD_NR	Module Not Ready; Indicating Module Operational Fault. Open-collector. LVTTL-O	2
RX_LOS	Loss of Signal indication. Logic 1 indicates loss of Signal. Open-collector. LVTTL-O	2
GND	Module Ground	1
GND	Module Ground	1
RD-	Receiver Inverted Data Output. CML-O	
RD+	Receiver Non-Inverted Data Output. CML-O	
GND	Module Ground	1
VCC2	+1.8V Power Supply (Not required).	3
P_DOWN/RST	Power down; When high, requires the module to limit power consumption to1.5W or below. 2-Wire serial interface must be functional in the low power mode.LVTTL-IReset; The falling edge initiates a complete reset of the module including the 2-	_
		3
		1
REFCLK+		-
REFCLK-		
GND	Module Ground	1
GND	Module Ground	1
TD-		
TD+	Transmitter Non-Inverted Data Input. CML-I	
GND	Module Ground	1
	GNDVee5MOD_DESEL//INTERRUPTTX_DISVCC5GNDVCC3VCC3VCC3SCLSDAMOD_AbsMOD_AbsMOD_NRRX_LOSGNDRX_LOSGNDVCC2P_DOWN/RSTVCC2VCC2GNDVCC2QNDREFCLK+GNDGNDTD-TD-TD-TD-	GND Module Ground Vee5 (not required) MOD_DESEL Module De-select; When Held low allows the module to respond to 2-wire serial interface. LVTL-1 /INTERUPT Interrupt; Indicates presence of an important condition which can be read via the 2-wire serial interface. LVTL-0 TX_DIS Transmitter Disable. Logic1 indicates laser output disabled, LVTL-1 VCC5 +5V Power Supply (Not required) GND Module Ground VCC3 +3.3V Power Supply MOD_Abs Indicates Module is not present. Grounded in the Module. LVTL-0 MOD_Abs Indicates Module is not present. Grounded in the Module. LVTL-0 RV Module Ground RD Receiver Inverted Data Output. CML-0 GND Module Ground

Notes:

- 1. Module ground pins GND are isolated from the module case and chassis ground within the module.
- 2. Open collector; should be pulled up with 4.7K-10Kohms to a voltage between 3.15V and 3.6V on the host board.
- 3. The pins are open within module.





Recommended Circuit Schematic



Mechanical Specifications

Small Form Factor Pluggable (XFP) transceivers are compatible with the dimensions defined by the XFP Multi-Sourcing Agreement (MSA).



EEPROM Information

Management Interface

XFP 2-wire serial interface is specified in the Chapter 4 of the XFP MSA specification. The XFP 2-wire serial interface is used for serial ID, digital diagnostics, and certain control functions. The 2-wire serial interface is mandatory for all XFP modules. The 2-wire serial interface address of the XFP module is 1010000X(A0h). In order to access to multiple modules on the same 2-wire serial bus, the XFP has a MOD_DESEL(module deselect pin). This pin (which is pull high or deselected in the module) must be held low by the host to select of interest and allow communication over 2-wire serial interface. The module must not respond to or accept 2-wire serial bus instructions unless it is selected.

XFP Management Interface

XFP Management interface is specified in the Chapter 5 of the XFP MSA specification. The Figure 1 shows the structure of the memory map. The normal 256 Byte address space is divided into lower and upper blocks of 128 Bytes. The lower block of 128 Byte is always directly available and is used for the diagnostics and control functions that must be accessed repeatedly. Multiple blocks of memories are available in the upper 128 Bytes of the address space. These are individually addressed through a table select Byte which the user enters into a location in the lower address space. The upper address space tables are used for less frequently accessed functions and control space for future standards definition.

EEPROM memory map specific data field description is as below:



About ProLabs

Our experience comes as standard; for over 15 years ProLabs has delivered optical connectivity solutions that give our customers freedom and choice through our ability to provide seamless interoperability. At the heart of our company is the ability to provide state-of-the-art optical transport and connectivity solutions that are compatible with over 90 optical switching and transport platforms.

Complete Portfolio of Network Solutions

ProLabs is focused on innovations in optical transport and connectivity. The combination of our knowledge of optics and networking equipment enables ProLabs to be your single source for optical transport and connectivity solutions from 100Mb to 400G while providing innovative solutions that increase network efficiency. We provide the optical connectivity expertise that is compatible with and enhances your switching and transport equipment.

Trusted Partner

Customer service is our number one value. ProLabs has invested in people, labs and manufacturing capacity to ensure that you get immediate answers to your questions and compatible product when needed. With Engineering and Manufacturing offices in the U.K. and U.S. augmented by field offices throughout the U.S., U.K. and Asia, ProLabs is able to be our customers best advocate 24 hours a day.



Contact Information ProLabs US Email: sales@prolabs.com Telephone: 952-852-0252

ProLabs UK

Email: salessupport@prolabs.com Telephone: +44 1285 719 600